


# DPA Video Conferencing and Webinar Solutions

## 6066 Subminiature Headset



- One-size-fits-all, headset fits securely and comfortably
- 2-way adjustable, non-reflective boom with locking system
- Unique, comfortable 3-point gripping system above, below and behind the ear
- New 90° cable management constructed to guide the cable and minimize cable breaks

The 6066 Subminiature Omnidirectional Headset Microphone combines DPA's renowned sound in a capsule just 3mm in diameter providing one of the most discrete solutions available. The 6066 is fully adjustable and comes in Black, Beige or Brown. Paired with either a simple XLR connector or the MMA-A Digital Interface, the 6066 Subminiature Headset provides a discrete, high-quality way to improve how you communicate with your audience.

### How to use the 6066 Subminiature Headset at home:

#### I have an Audio Interface

Simply use a DAD6001-BC Microdot-to-XLR adaptor to connect the microphone to your usual input.



#### I do not have an Audio Interface

Connect the headset to Channel 1 and the MMA-A to your computer with no drivers needed.

